

Quantec Accessible Toilet Alarm Kit c/w QT607, QT606S, QT605S & NC949

Part No. QT951



## **Overview**

A cost-effective expansion kit that adds true BS8300 compliant accessible toilet alarm functionality to a Quantec Addressable Call System.

Includes a QT607 ceiling pull unit, a QT605S reset point c/w confidence sounder, a Quantec slave overdoor light c/w sounder and an NC949 Accessible Toilet Sticker.

Allows people in distress to call for help quickly and easily.

Call acknowledgement function provides audible & visual feedback inside the WC that help is on the way (see Operation section below).

Staff can 'Accept' alarm calls at a Quantec display.

Multiple kits can be used on one Quantec system.

Includes a free MRSA resistant anti-bacterial pull cord pack (for a limited period only).

Backwards compatible.

Must be used in conjunction with at least one Quantec Controller.

**T** 01942 322744

## **Technical Specifications**

| Mains supply                    | Power derived from main QT601-2 Quantec Controller (not supplied).   |
|---------------------------------|--|
| Internal power supply           | N/A.   |
| Total output current limited to | N/A.   |
| Quiescent current               | Typically 6mA.   |
| Zone current                    | N/A.   |
| Alarm current                   | Less than 30mA (all QT951 devices).  |
| Max battery size and type       | An optional standby battery supply (2 x 12V 7Ah VRLA) can be connected at the main QT601-2 Quantec Controller, not supplied. |
| Auxiliary relays                | N/A. However optional QT612 Relay Output Devices can be connected to the Quantec network/wiring.                             |

Fire Industry Association

ISCE

(LPCB) 🙎

OHEMA



F 01942 829867 W www.c-tec.com

C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom

E sales@c-tec.co.uk



| Indicators                       | QT607 has a red Reassurance LED; QT605S has a red/green Reassurance LED; QT606S has twin red/green Alarm LEDs.   |
|----------------------------------|--|
| Controls                         | QT607 Ceiling pull activated by two pull cord bangles. QT605S has a Reset button. Call Accept function can be carried out at a Quantec Display (not supplied).     |
| Expansion connections            | N/A. However additional call and indicating devices can be connected to the Quantec network/wiring.  |
| Onboard Sounder                  | Yes (on QT605S and QT606S).  |
| Onboard Infrared Receiver        | No.  |
| Product dimensions (mm)          | 87 W x 87 H x 68 D (QT606S); 87 W x 87 H x 24 D (QT605S). Ceiling pull measures 93mm diameter x 27 D.  |
| Packaging dimensions (mm)        | 143 W x 96 H x 102 D mm (size of QT951 kit box containing all items).  |
| Construction & finish            | Plastic.   |
| IP Rating                        | IP41 (QT606S); IP40 (QT605S); IP21 (QT607).  |
| Weight                           | 0.30kg.  |
| Operating conditions/temperature | -5°C to +40°C. Max relative humidity: 95%.   |
| Notes                            | The QT951 is an expansion kit designed for use with Quantec Addressable Call Systems. It must be used in conjunction with at least one QT601-2 Quantec Controller. |





ISCE The Fathase of Sound and Communicatives Brighteen Supporting Member 1 - 1 C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom